

Technical change to BVFL and SVFL

Dear Madam or Sir,


the below listed articles will be supplied in a modified revision. Please pass this product information on to your employees and, if needed, to your customers. All modifications are performed for reasons of product improvements.

1. Initial situation

To connect a wire to the connector, the customer must push the actuator first

2. Technical change

In future the connector will be delivered with a press actuator, means the clamping point is open (wire ready)

Old version	New version
	
<p>Anschließen von flexiblen Leitern:</p> <ol style="list-style-type: none"> Klemmstelle öffnen: Drücken Sie mit dem Schlitzschraubendreher einzeln auf den Betätiger (Schieber/Pusher) bis dieser einrastet.  <ol style="list-style-type: none"> Leiter anschließen: Stecken Sie den Leiter, bis zum Anschlag, in die Klemmstelle ein.  <ol style="list-style-type: none"> Klemmstelle schließen: Verriegeln Sie die Klemmstelle durch senkrechten Druck auf den Betätiger (Schieber/Pusher). Beachten Sie dabei, dass der Leiter bis zum Anschlag eingesteckt ist und kontrollieren Sie durch leichten Zug an den Adern, dass die Klemmstelle sicher verriegelt ist. 	<p>Anschließen von flexiblen Leitern:</p> <ol style="list-style-type: none"> Klemmstelle öffnen: Drücken Sie mit dem Schlitzschraubendreher einzeln auf den Betätiger (Schieber/Pusher) bis dieser einrastet.  <p style="color: red; text-align: center;">Step deleted</p> <ol style="list-style-type: none"> Leiter anschließen: Stecken Sie den Leiter, bis zum Anschlag, in die Klemmstelle ein.  <ol style="list-style-type: none"> Klemmstelle schließen: Verriegeln Sie die Klemmstelle durch senkrechten Druck auf den Betätiger (Schieber/Pusher). Beachten Sie dabei, dass der Leiter bis zum Anschlag eingesteckt ist und kontrollieren Sie durch leichten Zug an den Adern, dass die Klemmstelle sicher verriegelt ist. 

3. Reason for change

- Increase customer benefit
- Time savings when connecting conductors
- Easier handling
- ideal for short stripped cables
- Thin conductors can be easily inserted into the open terminal point

4. Availability

- From 04.02.2019, the production will gradually be converted to the new version
- There will be no specific stock clearance
- Previously packaged items will continue to be delivered until inventory is exhausted
- Order-No. and price per 100pcs. won't be changed

5. Affected parts

Artikelnummer part number	Artikelbezeichnung part description
2549310000	BVFL 7.62HP/02/180 BCF/04R SN BK BX
2548870000	BVFL 7.62HP/02/180 SN BK BX
2549280000	BVFL 7.62HP/02/180F SN BK BX
2549320000	BVFL 7.62HP/02/180MF2 BCF/04R SN BK BX
1435390000	BVFL 7.62HP/02/180MF2 BCF/04R SNBK BX SO
2427310000	BVFL 7.62HP/02/180MF2 BCF/04R SNBK BX SO
2549300000	BVFL 7.62HP/02/180MF2 SN BK BX
1435370000	BVFL 7.62HP/02/180MF2 SN BK BX LRP
2549330000	BVFL 7.62HP/02/180MSF2 BCF/04R SN BK BX
2549400000	BVFL 7.62HP/03/180 BCF/04R SN BK BX
2549410000	BVFL 7.62HP/03/180 BCF/06R SN BK BX
2549420000	BVFL 7.62HP/03/180 BCF/08R SN BK BX
2548880000	BVFL 7.62HP/03/180 SN BK BX
2549340000	BVFL 7.62HP/03/180F SN BK BX
1435380000	BVFL 7.62HP/03/180MF2 BCF/06R SNBK BX SO
2575260000	BVFL 7.62HP/03/180MF2 BCF/06R SNBK BX SO
2549360000	BVFL 7.62HP/03/180MF2 SN BK BX
1435360000	BVFL 7.62HP/03/180MF2 SN BK BX LRP
2549460000	BVFL 7.62HP/03/180MF3 BCF/04R SN BK BX
2549470000	BVFL 7.62HP/03/180MF3 BCF/06R SN BK BX
2549480000	BVFL 7.62HP/03/180MF3 BCF/08R SN BK BX
2549370000	BVFL 7.62HP/03/180MF3 SN BK BX
1435350000	BVFL 7.62HP/03/180MF3 SN BK BX SO
2549540000	BVFL 7.62HP/03/180MSF3 BCF/04R SN BK BX
2549550000	BVFL 7.62HP/03/180MSF3 BCF/06R SN BK BX
2549560000	BVFL 7.62HP/03/180MSF3 BCF/08R SN BK BX
1547560000	BVFL 7.62HP/04/180 BCF/04R SN BK BX
2549430000	BVFL 7.62HP/04/180 BCF/06R SN BK BX
2549440000	BVFL 7.62HP/04/180 BCF/08R SN BK BX
1547520000	BVFL 7.62HP/04/180 SN BK BX
1547530000	BVFL 7.62HP/04/180F SN BK BX
1547540000	BVFL 7.62HP/04/180MF3 SN BK BX
2452210000	BVFL 7.62HP/04/180MF3 SN BK BX SO
2653030000	BVFL 7.62HP/04/180MF4 BCF/04 SN BK BX SO
2016150000	BVFL 7.62HP/04/180MF4 BCF/04 SN BK BX SO
2427960000	BVFL 7.62HP/04/180MF4 BCF/04 SN BK BX SO
2653020000	BVFL 7.62HP/04/180MF4 BCF/04 SN BK BX SO
2590720000	BVFL 7.62HP/04/180MF4 BCF/04 SNBK BX SO

1547590000	BVFL 7.62HP/04/180MF4 BCF/04R SN BK BX
2549490000	BVFL 7.62HP/04/180MF4 BCF/06R SN BK BX
2549500000	BVFL 7.62HP/04/180MF4 BCF/08R SN BK BX
2590770000	BVFL 7.62HP/04/180MSF4 BCF/04 SNBK BX SO
1547600000	BVFL 7.62HP/04/180MSF4 BCF/04R SN BK BX
2549570000	BVFL 7.62HP/04/180MSF4 BCF/06R SN BK BX
2549580000	BVFL 7.62HP/04/180MSF4 BCF/08R SN BK BX
2549450000	BVFL 7.62HP/05/180 BCF/04R SN BK BX
2548890000	BVFL 7.62HP/05/180 SN BK BX
2549350000	BVFL 7.62HP/05/180F SN BK BX
2549380000	BVFL 7.62HP/05/180MF3 SN BK BX
2522490000	BVFL 7.62HP/05/180MF3 SN BK BX LRP
2549510000	BVFL 7.62HP/05/180MF4 BCF/04R SN BK BX
2549520000	BVFL 7.62HP/05/180MF4 BCF/06R SN BK BX
2549530000	BVFL 7.62HP/05/180MF4 BCF/08R SN BK BX
2549390000	BVFL 7.62HP/05/180MF4 SN BK BX
2549590000	BVFL 7.62HP/05/180MSF4 BCF/04R SN BK BX
2549600000	BVFL 7.62HP/05/180MSF4 BCF/06R SN BK BX
2549610000	BVFL 7.62HP/05/180MSF4 BCF/08R SN BK BX
2007580000	BVFL 7.62HP/06/180 SN BK BX SO
1547570000	SVFL 7.62HP/04/180F SN BK BX
1547550000	SVFL 7.62HP/04/180G SN BK BX
1547580000	SVFL 7.62HP/04/180MF3 SN BK BX

We are very sorry for all the inconveniences caused and doing everything to adjust this product change as smooth as possible without big influence on delivery times and general functions.

For further questions please contact your sales office directly. All contacts for sales representatives are available here: www.weidmueller.com/contact

Best regards

Product Management

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16, 32758 Detmold, Germany

Weidmüller – Your partner in Industrial Connectivity
We look forward to sharing ideas with you – **Let's connect.**